



This bar can be mounted horizontally, vertically or diagonally for use individually or in combination with other grab bars. All bars are 1 1/4" in diameter with concealed screw flanges and are 18 gauge. Additional bar configurations, finishes and coatings are available by special order.


Standard Lengths:

12" (305mm)	30" (762mm)	42" (1067mm)
16" (406mm)	32" (813mm)	48" (1219mm)
18" (457mm)	36" (914mm)	52" (1321mm)
24" (610mm)	40" (1016mm)	54" (1372mm)

FINISHES



Field Installation of Grab Bars



Installing grab bars in **existing** Fiber-Fab bathtubs and showers does not require additional backing. Because Fiber-Fab's units have an extremely high content of resin and fiberglass and low filler content, the strength and rigidity needed to support the mounting of grab bars are inherent to the product (**Fiber-Fab is the only manufacturer that can make this claim**).

In mounting the grab bar(s), we recommend using a stainless steel, #10 wood screw, 2" long with threads all the way to the head of screw.



H703PH Folding Shower Seat

Frame is stainless steel Type 304, 1" x 18 gauge satin finish. Legs angle into base of wall for rigid support. When not in use, seat folds up against wall to conserve space and thumb screw holds it in place. Seat measures 18" long and projects 15 1/2" from wall.




HSH404-## Four-Legged, Wheelchair Transfer Seat

This seat complies with ADA requirements. Use this seat for retrofitting an existing barrier-free shower or in commercial applications where weights greater than 350 pounds may be encountered. Seat and legs fold up against the wall when the seat is not needed. Fits Fiber-Fab Models # 38H1, 40H1KD, 48H1, 60H1, 60H1KD and 63H1.



Adult Changing Table (H730PHMFF)

This table is designed to comply with ADA requirements where special needs exist in schools, hospitals and other applications. Table can be folded up when not in use, measures 55" long and extends from the wall 16".



Accessories
Fiber-Fab Inc.

