



Haws[®]

model **7260B-7270B**

Eye/Face Washes

FEATURES & BENEFITS

STRAINERS/FILTERS

Chrome-plated brass in-line 50 x 50 mesh water strainer prevents debris from reaching the eyewash so the unit stays functioning at its best. Strainer is easily serviceable.

QUALITY CONTROL

Eye/face wash and valve assembly is pre-built and fully water/pressure tested to ensure no leaks and proper function which ultimately reduces installation time and gives the end contractor an added peace of mind. Unit also ships with pre-assembled cast-aluminum wall bracket to assist in the installation process.

EYE/FACE WASH

AXION MSRT™ eye/face wash head (patent pending) uses an inverted directional laminar flow to sweep contaminants away from the vulnerable nasal cavity.

ANTIMICROBIAL TREATED

AXION MSRT™ eye/face head is antimicrobially treated using the natural protection of silver. Impregnating these components with silver helps protect the head against the growth of mold and mildew on the treated components. AXION MSRT™ is the only eye/face product on the market to feature antimicrobial protection.

BOWL

The 11" round green ABS plastic receptor is resistant to damage from alkalis, salt solutions, oils and most acids.



SPECIFICATIONS

Model 7260B-7270B wall mounted eye/face wash shall include a green ABS plastic 11" bowl, an antimicrobially treated AXION MSRT™ eye/face wash head to help protect against the growth of mold and mildew on the treated components, and shall feature inverted directional laminar flow which achieves zero vertical velocity supplied by an integral 3.7 gpm flow control, chrome-plated brass stay-open ball valve equipped with stainless steel ball and stem, and chrome-plated brass in-line 50 x 50 mesh water strainer. Unit shall also include cast-aluminum chromate protected wall bracket, yellow plastic pop-off dust cover for eyewash head, universal sign, 1/2" IPS inlet, and 1-1/4" IPS waste.

APPLICATIONS

Where the eyes of any person may be exposed to injurious or corrosive materials, suitable facilities for quick flushing and cleansing of the eyes must be provided within the work area for immediate emergency use. Emergency eyewash facilities shall be in unobstructed and accessible locations that require no more than 10 seconds for the injured person to reach.

Model 7260B-7270B is certified by CSA & IAPMO to meet the ANSI Z358.1-2009 Standard for Emergency Eyewash and Shower Equipment.

OPTIONS

- ❑ Tempered Water Blending Systems: Model TWBS.EW.H, prepackaged instantaneous electrical water heater, 480 VAC/3 phase/18 KW, fully engineered and tested system with fail-safe features to produce up to 5 gpm tempered water for eye washes.
- ❑ Repair Kit: Model VRKEWSTR is a repair kit for SP507 and SP509. Includes screen and gasket.
- ❑ Dust Cover: Model 9102 is a stainless steel cover that protects the eyewash heads as well as the bowl. Pushing the stainless steel flag will activate the unit while raising the dust cover.
- ❑ Tempered Water Blending Systems: Model TWBS.EW, prepackaged, fully engineered and tested hot and cold water blending system with fail-safe features to produce up to 5 gpm tempered water for eye/face washes (Pat.# 5,350,112).

To see all options for this model, visit www.hawsc.com

